

Product Information:

Wipes Sensitive 915

Removes uncured sealant from all surfaces


General description & application:

Wipes Sensitive 915 is specially developed for removal of non-cured sealant of e.g. silicone, PU and MS, from all types of surfaces and can also be used for oil, grease, dirt etc

Wipes Sensitive 915 can be used for degreasing prior to sealing or adhesion

Wipes Sensitive 915 can be used on most surfaces like metals, painted surfaces, plastic etc. The product is supplied in a special design container that prevents the wipes from drying out.



Member of  Danish Association of Sealant Applicators & Manufacturers.

Physical / chemical properties:

Type: Paper napkin
 Shelf life: Minimum 2 years in unopened packaging if stored cool and dry.
 Packaging:

Art. no.	Size
30077	200 pcs box
30072	80 pcs box

Directions for use:

Preparation: Wipes Sensitive 915 can be used to remove most types of uncured sealant, glue, oil, dirt and grease. For extra cleaning ability, Pro Wipes 916 or Pro Wipes Extra 917 can be used.

If the product is used for degreasing, it is important that the wipes is changed regularly before it becomes too dirty.

Wipes Sensitive 915 may damage gaskets, lacquered or painted surfaces, protective coverings and rubber materials. Always carry out a test before use.

After use: Immediately after degreasing with the wet wipe the surfaces should be dried of with a clean dry cloth prior to sealing or adhesion.

Health and Safety:

For further information on safety, refer to product safety data sheet.

The information and data contained in this Product Information sheet are based on extensive laboratory testing and our practical experiences and are meant for helping the user to find optimum working methods. As the conditions at the user are beyond our control, we make no warranties concerning the results, achieved by the products. The information's in this Product Information sheet are typical values, intended as a guideline. They should not be regarded as product specifications. Please also refer to our standard sales conditions and terms of delivery.

**DANA LIM A/S - KØBENHAVNSVEJ 220 - DK-4600 KØGE – DENMARK – INFO@DANALIM.DK
 PH. (+45) 56 64 00 70 - TECHNICAL SERVICE PH. (+45) 56 64 00 75**

